High intensity White Line Lights Product Datasheet





LL167 Series Description

The LL167 is engineered to provide optimal power on target. As with the LL137, it offers a scalable length design, multiple lens options, and an embedded controller.

The LL167 housing is identical to that of the LL137 and it also deploys an embedded control circuit for 0-10 volt DC analog dimming and gating on/off. The "C1" light may be ordered for use with the DCS controllers; the optional "IC" model includes manual analog dimming potentiometers for individual control of each 6" segment in the light.

The LL167 differs from the LL137 in offering only a white version standard that offers more line intensity on target. It differs from the LL330 in IP50 only rating and less intensity on target.



High Intensity



Scalable Linear Design



Uniformity Control



Multiple Focal Lengths



1-2 Week BTO Lead Times Typical

LL167 SeriesProduct Datasheet

High Intensity White Line Lights



General Information

			C	General Specifications		
Category	Specification			Detail		
	Available Wavelengths			White		
Optical	Available Lensi	ing		4 Focal Lengths		
	Available Light	Conditioning		None		
Electrical	Power Consum	nption Info		See Power Requirements on Page 7		
Liectrical	Cable Info			80" -0/+6" Long (2 m -0/+150 mm), 105 °C Rated, Foil Shield w/ Drain		
		Standard	Length	3.24"(82.3mm) to 96.24"(2444.5mm)		
	Sizing Info		Width	1.98"(50.2mm)	See Page 6 for More Details	
Mechanical			Height	G lens: 3.70"(93.9mm); D lens: 3.80"(96.5mm); E lens: 4.05"(102.8mm); F lens: 4.55"(115.5mm)		
Wechanical	Weight Info (Standard)			~ 2.20 lbs (~998 g) per 6" Unit Length		
	Mounting Info			M6 Mounting Nut Channel		
	Material Info			Anodized Aluminum Housing, Acrylic Window, Nylon Strain Relief, PVC Cable Jacket, Steel Black Oxide & Zinc Plated Steel Fasteners		
Thermal	Operating Case Temperatures		es	25 °C to 60 °C		
Hermai	Operating Ambient Temperatures			0 °C to 35 °C		
	Compliance			CE, RoHS, IEC 62471		
Certification	IP Rating			IP50		
	Lumen Maintenance - White Only			L70 (50,000 Hours)		

LL167 Series

Product Datasheet

High Intensity White Line Lights



General Information - Continued

Part Number Key

Model	Lens Focus	Emitting Length (in)	-	Peak Wavelength	Connector/Control
LL167	X	XX	-	XXX	XX
LL167	D (Converging)	06 to 96		WHI (white)	C1 ²
	E (Converging)	(06" increments from 06" to 96")			IC ¹
	F (Converging)				24
	G (Collimating)				
more info on page	4	6		4	7

Example Part Numbers:

LL167D12-WHIC1 LL167G24-WHIIC ¹ See Electrical Specs for details on IC option with LL167 ² Not available over 12" emitting length

In Stock

Unavailable

Lead Times

Stock products ship within three days.
Build-to-Order custom products ship within one to two weeks.

Configurator




Need a build-to-order custom lighting solution in 2 weeks or less? Advanced Illumination's online configurator helps you tailor our LL167 High Intensity White Line Lights to your specific needs. For a guided configuration, visit our online configurator.



Optical Information

Intensity Characteristics




Intensity distribution sample image was taken with a 12-inch white LL167 unit with a D lens.

Illuminance data was collected using a 12-inch white LL167 unit.

Line Width


Uniformity

Line Width vs Working Distance




Line width data was collected using a 12-inch white LL167 unit.

Longitudinal Intensity Distribution Profile at 50 mm Working Distance



Longitudinal intensity distribution data was collected using a 12-inch white LL167 unit with a G lens.

White Spectral Profile



White LED illumination is the most commonly used machine vision lighting configuration. It is often the default choice when specific features of interest do not require color-based highlighting. However, white LEDs can vary in color temperature between different lighting families, which can impact machine vision systems, specifically when matching white light sources.

The LL167 Series white LEDs have a relatively cool color correlated temperature (CCT) of $6500~\rm{K}$.

For a more detailed look at the white spectral data, download the csv file of the raw spectral values and refer to our Product Spectra Distribution Charts PDF.

Disclaimer. The measurements provided above are for approximations only and may vary depending on the method of measurement and the specific configuration being measured

LL167 SeriesProduct Datasheet

High Intensity White Line Lights



Optical Information - Continued

Photobiological Risk Factors

Group	Description	Affected Wavelengths
Exempt	No Photobiological Hazard	N/A
Group 1	No Photobiological hazard under normal behavioral limitations	WHI
Group 2	Does not pose a hazard due to aversion response to bright light or thermal discomfort	N/A

Advanced Illumination's lighting products have been tested and classified to IEC standards by accredited testing services. For more information on photobiological risk factors, please view the following PDF: https://www.advancedillumination.com/wp-content/uploads/2019/04/IEC-040119.pdf

Cleaning Guidelines



To clean our light's optics, it is best to only clean when necessary. Dusting is always the first step in cleaning your optics. Wiping a dusty optic is like cleaning it with sandpaper. So always dust with a canned air duster or compressed and filtered air before wiping any optic. If the dusted optic has no visible stains after you dust it, then remember: "If it's not dirty, don't clean it." Avoid wiping optics when possible.


If dusting did not clean the lens or the lens has stains, use only de-ionized water and mild dish soap with a low lint cloth designed for optics to avoid damage to the optic by any harsh chemicals.

Polarizers, beam splitters and collimated films should never be wiped with any type of cloth or solvent, only use the air dusting method to clean these types of optics.

The aluminum housing can be wiped down when dusting is not a sufficient means to thoroughly clean.



Mechanical Information



For full installation drawings and complete CAD models of this non-sealed configuration, please visit the downloads section of the product webpage.

Sizing Chart

Part Number		Length (Inches)		ı	Length (Millimeters)		Dower Ontions
Part Number	Unit	D/E/F Lens	G Lens	Unit	D/E/F Lens	G Lens	Power Options
LL167X03	3.24	3.040	3.000	82.296	77.216	76.200	C1 / 24 / IC
LL167X06	6.24	6.000	6.000	158.496	152.400	152.400	C1 / 24 / IC
LL167X12	12.24	12.000	12.000	310.896	304.800	304.800	C1 / 24 / IC
LL167X18	18.24	18.000	18.000	463.296	457.200	457.200	C1 / 24 / IC
LL167X24	24.24	24.000	24.000	615.696	609.600	609.600	24 / IC
LL167X30	30.24	30.000	30.000	768.096	762.000	762.000	24 / IC
LL167X36	36.24	36.000	35.944	920.496	914.400	912.978	24 / IC
LL167X42	42.24	42.000	41.934	1072.896	1066.800	1065.124	24 / IC
LL167X48	48.24	48.000	47.589	1225.296	1219.200	1208.761	24 / IC
LL167X54	54.24	54.000	53.915	1377.696	1371.600	1369.441	24 / IC
LL167X60	60.24	60.000	59.906	1530.096	1524.000	1521.612	24 / IC
LL167X66	66.24	66.000	65.896	1682.496	1676.400	1673.758	24 / IC
LL167X72	72.24	72.000	71.887	1834.896	1828.800	1825.930	24 / IC
LL167X78	78.24	78.000	77.878	1987.296	1981.200	1978.101	24 / IC
LL167X84	84.24	84.000	83.868	2139.696	2133.600	2130.247	24 / IC
LL167X90	90.24	90.000	89.859	2292.096	2286.000	2282.419	24 / IC
LL167X96	96.24	96.000	95.849	2444.496	2438.400	2434.565	24 / IC

High Intensity White Line Lights



Electrical Information

Power Requirements

Current Required for Power Supply Sizing

Wavelengths	Configured w/ Voltage Drive (24)	Configured w/ Standard Controller (C1, C5, IC, I3, I3S)
WHI	0.760A per 6 inch increment	0.760A per 6 inch increment

Note: All Advanced Illumination lights and controllers are nominally powered by 24V DC unless otherwise noted. Strobe overdriving with controller based models may require more current and voltage overhead. The values above do not include background current draw from the controller (~100 mA total).

Control Options

Controller Image	Controller Details	Connector Image

DCS Single Output Controller - Compatible with C1 Configurations

PN: DCS-100E



The DCS-100E is a compact, din-rail mounted general-purpose external controller with one C1 output connector, wired with three channels. Capable of providing single channel control or multi-channel control for RGB compatible lights.

Output Power: 90 W Max Continuous, 540 W Max Pulsed (Overdrive Strobe)

Output Current: 4.5A Max Continuous, 15 A Max Pulsed

I/Os: 3 External Trigger Inputs

Interface: 10/100 Ethernet with Software and browser-based GUIs. SDKs are also available.

For more information about our DCS-100E, please visit the controller product page.

DCS Triple Output Controller - Compatible with C1 Configurations

PN: DCS-103E

The DCS-103E is a din-rail mounted general-purpose multi-light controller with three C1 output connectors. Capable of driving three lights in sync or asynchronously.

Output Power: 30 W Max Continuous / Output, 180 W Max Pulsed / Output Output Current: 1.5A Max Continuous / Output, 5 A Max Pulsed / Output

I/Os: 3 External Trigger Inputs

Interface: 10/100 Ethernet with Software and browser-based GUIs. SDKs are also available.

For more information about our DCS-103E, please visit the controller product page.





Electrical Information - Continued

Control Options - Continued


Controller Image Controller Details Connector Image


LL167 Embedded Controller - Continuous Only - IC Configurations

The IC on the LL167 is an embedded controller which allows for control of light intensity per 6" (152 mm) segment. Each segment is adjusted using a potentiometer located on each 6" segment. See the figure below for illustration:









Controlling each 6" (152mm) section independently and making the center of the line less bright and the outside of the immediate camera viewing radius brighter ultimately results in better imaging.

Better imaging occurs because the camera can see very well in its area of focus, but outside that area the camera doesn't focus as well without brighter illumination.

We recommend using this control option for LL167 $\,$ lights over 24" (610mm) in length.



24V Driver - Continuous Only - 24 Configurations *PN: N/A*

24V option allows lights to operate continuous output with 24V connection and no additional controllers.

Modes: Continuous, can be wired to some 3rd party controllers or external relays for gated operation **Interface:** Direct cable (flying leads or connector options)



High Intensity White Line Lights



Electrical Information - Continued

24V Option Wiring Information

Flying Lead Functions

Wire Color	24V Functions
BROWN	24V DC
WHITE	0 - 10V Analog Control
BLUE	DC GND
BLACK	N/A
GRAY	N/A

The functions above are only applicable when ordering a 24V power configuration.

Accessories

Category	Accessory Image	Accessory Detail
Power Supply		24 Volt DC Power Supply PN: PS24-TL This convenient power source is a universal AC input switching power supply with a regulated output DC current. The power supply comes with an LED Power Indicator, tinned leads marked Positive (+) and Negative (-) and 2 WAGO connectors for simplified assembly. For more information about our 24 Volt DC Power Supply, please visit this webpage.
Dimmer		Manual Dimming Accessory for the IC, I3 and I3s PN: DCS-MP The DCS-MP is a 30-position potentiometer, detented for precision level control and provides repeatable dimming with cable inline controllers. Features include DIN-rail mountable, a flip up cover to prevent accidental adjustments, spring clamp wiring terminal for flying leads or an M12 connector for use with the IC or I3/I3S Inline Controllers. For more information about our Manual Dimming Accessory please visit this webpage.

Extension Cable



DCS-100E/103E Extension Cable, Single Light Power Cable - C1 Configuration PN: LC-XX-S

This extension cable was designed for applications requiring power cables longer than the standard 2 meters provided with Ai lights. This single light cable features a single male and single female 7 pin locking connector (C1) and can be purchased in 3 - 15-meter lengths.

For more information about our DCS-100E/103E Extension Cable, Single Output, please visit this webpage.

Extension Cable



DCS-100E/103E Extension Cable, Dual Light Power Cable - C1 Configuration PN: LC-XX-Y

This extension cable was designed for applications requiring two identical lights to be powered through a single controller. These Y cables feature a single male and dual female 7 pin locking connectors (C1) and can be purchased in 3 - 15-meter lengths. See attached spec sheet for compatible light configuration.

For more information about our DCS-100E/103E Extension Cable, Split Output, please visit this webpage.

Camera Lens Band Pass Filters PN: BPXXX-YYY

Filters



Eliminating all but a narrow band of light (+/- 40nm) centered on the specified wavelength, band pass filters are used to enhance colors, or to stop unwanted ambient light from reaching the camera. Filtering can replace existing shrouds, simplifying the physical set up of an inspection site. Ai offers 635nm and 660nm band pass filters to fit several different lens sizes.

For more information about our Camera Lens Band Pass Filters, please visit this webpage.

LL167 SeriesProduct Datasheet

High Intensity White Line Lights



Additional Information

Warranty

Every Advanced illumination, Inc. (Ai) product is thoroughly inspected and tested before leaving the factory. Products are warranted to be free of defects in workmanship and materials for a period of FIVE YEARS from the original date of purchase. Should a defect develop during this period, customers may return the complete product, freight prepaid, to one of Ai's distributors or to the Ai factory. All product warranty returns require a Return Merchandise Authorization (RMA) number which is obtained from Customer Service. The RMA number must be clearly marked on the outside of the package. Ai will inspect the unit, and if a defect is found will, at our option, repair or replace the product without charge. Ai disclaims liability for any implied warranties, including implied warranties of "merchantability" and "fitness for a specific purpose." For products under warranty that have since been discontinued, Ai will make an effort to replace with equivalent parts; for circumstances that do not allow for equivalent replacement, Ai reserves the right to repair or replace these products with an updated version. Ai cannot be held responsible for the unauthorized or inappropriate use of its products. Any unauthorized repair or modifications will result in a voided warranty. No Liability for Consequential Damages: In no event shall Ai be liable for any consequential, special, incidental, or indirect damages of any kind arising from the sale or use of the products.

Compliancy

Our lighting products are designed and tested to meet CE, RoHS, and IEC standards. As a global ISO 9001 certified company, we understand the importance of compliance and perform accelerated testing on every product before shipment. For more information on our compliance standards, please see our compliancy documentation here: https://www.advancedillumination.com/services/compliance-statements/

Electromagnetic Compatibility

This product was tested and complies with the regulatory requirements and limits for electromagnetic compatibility (EMC) as stated in the product specifications. These requirements and limits are designed to provide reasonable protection against harmful interference only when the product is operated in its intended industrial electromagnetic environment. To minimize the potential for electromagnetic interference or unacceptable performance degradation, install and use this product in strict accordance with the instructions in the product documentation.

Customer Service

For information on existing orders, or to make an order adjustment, contact us Monday through Friday 8:00 am to 5:00 pm ET or send an email to orders@advancedillumination.com.

Company Information

Advanced Illumination
440 State Garage Road, Rochester, VT 05767
Phone: +1 (802) 767 3830
Fax: +1 (802) 767 2636
Email: info@advancedillumination.com
Web: advancedillumination.com
© 2023 Advanced illumination Inc. All rights reserved